

[All Products](#) / [Optics](#) / [Optical Filters](#) / [Machine Vision Filters](#) / [Color Filters](#)

Mounted Machine Vision Filters



- Optimized for Use with Popular LEDs
- Multiple Mounting Sizes and Threads Available to Ease System Compatibility
- $\geq 85\%$ Transmission
- [TECHSPEC® High Performance Mounted Machine Vision Filters](#) and [Mounted Color Filters](#) Also Available

Common Specifications

Physical & Mechanical Properties

Construction:

Mounted in Black Anodized Ring

Technical Information

Products

Filter Thread	Color	CWL (nm)	FWHM (nm)	Stock Number	Price	Buy
M77 x 0.75	NUV	324.00	105.00	#21-400	€430,00 Qty 10+ €408,50	3-4 days
#70-534 New						
						
New						
-	NUV	324.00	105.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€113,00 Qty 10+ €107,35	3-4 days
#70-535 New						
						
New						
-	Blue	470.00	85.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€113,00 Qty 10+ €107,35	Contact Us

[#70-536 New](#)



New

-	Cyan	505.00	90.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€113,00 Qty 10+ €107,35	3-4 days
---	------	--------	-------	--	----------------------------	----------

[#70-537 New](#)



New

-	Green	525.00	80.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€113,00 Qty 10+ €107,35	3-4 days
---	-------	--------	-------	--	----------------------------	----------

[#70-538 New](#)



New

-	-	530.00	120.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€113,00 Qty 10+ €107,35	3-4 days
---	---	--------	--------	--	----------------------------	----------

[#70-539 New](#)



New

-	VIS	550.00	300.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€104,00 Qty 10+ €98,80	Contact Us
---	-----	--------	--------	--	---------------------------	------------

[#70-540 New](#)



New

-	Orange	590.00	70.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€113,00 Qty 10+ €107,35	3-4 days
---	--------	--------	-------	--	----------------------------	----------

[#70-541 New](#)



New

-	Light Red	635.00	60.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€104,00 Qty 10+ €98,80	3-4 days
---	-----------	--------	-------	--	---------------------------	----------

[#70-542 New](#)



New

-	Dark Red	660.00	70.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€104,00 Qty 10+ €98,80	3-4 days
---	----------	--------	-------	--	---------------------------	----------

[#70-543 New](#)



New

-	NIR-IR	800.00	315.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€104,00 Qty 10+ €98,80	3-4 days
---	--------	--------	--------	--	---------------------------	----------

[#70-544 New](#)



New

-	SWIR	1,000.00	150.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€221,00 Qty 10+ €209,95	3-4 days
---	------	----------	--------	--	----------------------------	----------

[#70-545 New](#)



New

-	SWIR	1,550.00	190.00	Launched on our website before appearing in our latest print catalogs. Be the first to buy before anyone else!	€342,00 Qty 10+ €324,90	3-4 days
---	------	----------	--------	--	----------------------------	----------

M77 x 0.75	Blue	470.00	85.00	#21-401	€430,00 Qty 10+ €408,50	3-4 days
M77 x 0.75	Cyan	505.00	90.00	#21-402	€430,00 Qty 10+ €408,50	3-4 days
M77 x 0.75	Green	525.00	80.00	#21-403	€430,00 Qty 10+ €408,50	3-4 days
M77 x 0.75	Vis	550.00	300.00	#21-404	€387,00 Qty 10+ €367,65	Contact Us
M77 x 0.75	Orange	590.00	75.00	#21-405	€430,00 Qty 10+ €408,50	3-4 days
M77 x 0.75	Light Red	635.00	60.00	#21-406	€387,00 Qty 10+ €367,65	3-4 days
M77 x 0.75	Dark Red	660.00	60.00	#21-407	€387,00 Qty 10+ €367,65	3-4 days
M77 x 0.75	IR	850.00	160.00	#21-408	€387,00 Qty 10+ €367,65	3-4 days
M39 x 0.50	NUV	324.00	105.00	#21-417	€185,00 Qty 10+ €175,75	3-4 days
M39 x 0.50	Blue	470.00	85.00	#21-418	€185,00 Qty 10+ €175,75	3-4 days
M39 x 0.50	Cyan	505.00	90.00	#21-419	€185,00 Qty 10+ €175,75	3-4 days
M39 x 0.50	Green	525.00	80.00	#21-420	€185,00 Qty 10+ €175,75	3-4 days
M39 x 0.50	Vis	550.00	300.00	#21-421	€167,00 Qty 10+ €158,65	3-4 days

M39 x 0.50	Orange	590.00	75.00	#21-422	€185,00 Qty 10+ €175,75	3-4 days
M39 x 0.50	Light Red	635.00	60.00	#21-423	€167,00 Qty 10+ €158,65	3-4 days
M39 x 0.50	Dark Red	660.00	60.00	#21-424	€167,00 Qty 10+ €158,65	3-4 days
M39 x 0.50	IR	850.00	160.00	#21-425	€167,00 Qty 10+ €158,65	3-4 days
M49 x 0.75	NUV	324.00	105.00	#21-434	€209,00 Qty 10+ €198,55	3-4 days
M49 x 0.75	Blue	470.00	85.00	#21-435	€209,00 Qty 10+ €198,55	3-4 days
M49 x 0.75	Cyan	505.00	90.00	#21-436	€209,00 Qty 10+ €198,55	3-4 days
M49 x 0.75	Green	525.00	80.00	#21-437	€209,00 Qty 10+ €198,55	3-4 days
M49 x 0.75	Vis	550.00	300.00	#21-438	€188,00 Qty 10+ €178,60	3-4 days
M49 x 0.75	Orange	590.00	75.00	#21-439	€209,00 Qty 10+ €198,55	3-4 days
M49 x 0.75	Light Red	635.00	60.00	#21-440	€188,00 Qty 10+ €178,60	3-4 days
M49 x 0.75	Dark Red	660.00	60.00	#21-441	€188,00 Qty 10+ €178,60	3-4 days
M49 x 0.75	IR	850.00	160.00	#21-442	€188,00 Qty 10+ €178,60	3-4 days
M67 x 0.75	NUV	324.00	105.00	#21-451	€336,00 Qty 10+ €319,20	3-4 days
M67 x 0.75	Blue	470.00	85.00	#21-452	€336,00 Qty 10+ €319,20	3-4 days
M67 x 0.75	Cyan	505.00	90.00	#21-453	€336,00 Qty 10+ €319,20	3-4 days
M67 x 0.75	Green	525.00	80.00	#21-454	€336,00 Qty 10+ €319,20	3-4 days
M67 x 0.75	Vis	550.00	300.00	#21-455	€302,00 Qty 10+ €286,90	3-4 days
M67 x 0.75	Orange	590.00	75.00	#21-456	€336,00 Qty 10+ €319,20	3-4 days

M67 x 0.75	Light Red	635.00	60.00	#21-457	€302,00 Qty 10+ €286,90	3-4 days
M67 x 0.75	Dark Red	660.00	60.00	#21-458	€302,00 Qty 10+ €286,90	3-4 days
M67 x 0.75	IR	850.00	160.00	#21-459	€302,00 Qty 10+ €286,90	3-4 days
M52 x 0.75	NUV	324.00	105.00	#21-468	€215,00 Qty 10+ €204,25	3-4 days
M52 x 0.75	Blue	470.00	85.00	#21-469	€215,00 Qty 10+ €204,25	3-4 days
M52 x 0.75	Cyan	505.00	90.00	#21-470	€215,00 Qty 10+ €204,25	3-4 days
M52 x 0.75	Green	525.00	80.00	#21-471	€215,00 Qty 10+ €204,25	3-4 days
M52 x 0.75	Vis	550.00	300.00	#21-472	€194,00 Qty 10+ €184,30	3-4 days
M52 x 0.75	Orange	590.00	75.00	#21-473	€215,00 Qty 10+ €204,25	3-4 days
M52 x 0.75	Light Red	635.00	60.00	#21-474	€194,00 Qty 10+ €184,30	3-4 days
M52 x 0.75	Dark Red	660.00	60.00	#21-475	€194,00 Qty 10+ €184,30	3-4 days
M52 x 0.75	IR	850.00	160.00	#21-476	€194,00 Qty 10+ €184,30	3-4 days
M55 x 0.75	NUV	324.00	105.00	#21-485	€225,00 Qty 10+ €213,75	3-4 days
M55 x 0.75	Blue	470.00	85.00	#21-486	€225,00 Qty 10+ €213,75	3-4 days
M55 x 0.75	Cyan	505.00	90.00	#21-487	€225,00 Qty 10+ €213,75	3-4 days
M55 x 0.75	Green	525.00	80.00	#21-488	€225,00 Qty 10+ €213,75	3-4 days
M55 x 0.75	Vis	550.00	300.00	#21-489	€203,00 Qty 10+ €192,85	3-4 days
M55 x 0.75	Orange	590.00	75.00	#21-490	€225,00 Qty 10+ €213,75	3-4 days
M55 x 0.75	Light Red	635.00	60.00	#21-491	€203,00 Qty 10+ €192,85	3-4 days

M55 x 0.75	Dark Red	660.00	60.00	#21-492	€203,00 Qty 10+ €192,85	3-4 days
M55 x 0.75	IR	850.00	160.00	#21-493	€203,00 Qty 10+ €192,85	3-4 days
M55 x 0.75	SWIR	940.00	55.00	#28-794	€268,00	3-4 days
M55 x 0.75	SWIR	1,000.00	150.00	#28-805	€463,00	3-4 days
M55 x 0.75	SWIR	1,070.00	-	#28-860	€364,00	3-4 days
M55 x 0.75	SWIR	1,300.00	35.00	#28-827	€499,00	3-4 days
M55 x 0.75	SWIR	1,450.00	35.00	#28-838	€499,00	3-4 days
M55 x 0.75	SWIR	1,475.00	-	#28-871	€364,00	3-4 days
M55 x 0.75	SWIR	1,550.00	190.00	#28-816	€463,00	3-4 days
M55 x 0.75	SWIR	1,550.00	35.00	#28-849	€499,00	3-4 days
M86 x 0.75	NUV	324.00	105.00	#21-502	€581,00 Qty 10+ €551,95	3-4 days
M86 x 0.75	Blue	470.00	85.00	#21-503	€581,00 Qty 10+ €551,95	3-4 days
M86 x 0.75	Cyan	505.00	90.00	#21-504	€581,00 Qty 10+ €551,95	3-4 days
M86 x 0.75	Green	525.00	80.00	#21-505	€581,00 Qty 10+ €551,95	3-4 days
M86 x 0.75	Vis	550.00	300.00	#21-506	€523,00 Qty 10+ €496,85	3-4 days
M86 x 0.75	Orange	590.00	75.00	#21-507	€581,00 Qty 10+ €551,95	3-4 days
M86 x 0.75	Light Red	635.00	60.00	#21-508	€523,00 Qty 10+ €496,85	3-4 days
M86 x 0.75	Dark Red	660.00	60.00	#21-509	€523,00 Qty 10+ €496,85	3-4 days
M86 x 0.75	IR	850.00	160.00	#21-510	€523,00 Qty 10+ €496,85	3-4 days

M22 x 0.75	NUV	324.00	105.00	#21-519	€168,00 Qty 10+ €159,60	3-4 days
M22 x 0.75	Blue	470.00	85.00	#21-520	€168,00 Qty 10+ €159,60	3-4 days
M22 x 0.75	Cyan	505.00	90.00	#21-521	€168,00 Qty 10+ €159,60	3-4 days
M22 x 0.75	Green	525.00	80.00	#21-522	€168,00 Qty 10+ €159,60	3-4 days
M22 x 0.75	Vis	550.00	300.00	#21-523	€154,00 Qty 10+ €146,30	3-4 days
M22 x 0.75	Orange	590.00	75.00	#21-524	€168,00 Qty 10+ €159,60	3-4 days
M22 x 0.75	Light Red	635.00	60.00	#21-525	€154,00 Qty 10+ €146,30	3-4 days
M22 x 0.75	Dark Red	660.00	60.00	#21-526	€154,00 Qty 10+ €146,30	3-4 days
M22 x 0.75	IR	850.00	160.00	#21-527	€154,00 Qty 10+ €146,30	3-4 days
M22.5 x 0.50	NUV	324.00	105.00	#21-536	€135,00 Qty 10+ €128,25	3-4 days
M22.5 x 0.50	Blue	470.00	85.00	#21-537	€135,00 Qty 10+ €128,25	3-4 days
M22.5 x 0.50	Cyan	505.00	90.00	#21-538	€135,00 Qty 10+ €128,25	3-4 days
M22.5 x 0.50	Green	525.00	80.00	#21-539	€135,00 Qty 10+ €128,25	3-4 days
M22.5 x 0.50	Vis	550.00	300.00	#21-540	€121,00 Qty 10+ €114,95	3-4 days
M22.5 x 0.50	Orange	590.00	75.00	#21-541	€135,00 Qty 10+ €128,25	3-4 days
M22.5 x 0.50	Light Red	635.00	60.00	#21-542	€121,00 Qty 10+ €114,95	3-4 days
M22.5 x 0.50	Dark Red	660.00	60.00	#21-543	€121,00 Qty 10+ €114,95	3-4 days
M22.5 x 0.50	IR	850.00	160.00	#21-544	€121,00 Qty 10+ €114,95	3-4 days

M37 x 0.75	NUV	324.00	105.00	#21-553	€168,00 Qty 10+ €159,60	3-4 days
M37 x 0.75	Blue	470.00	85.00	#21-554	€168,00 Qty 10+ €159,60	Contact Us
M37 x 0.75	Cyan	505.00	90.00	#21-555	€168,00 Qty 10+ €159,60	3-4 days
M37 x 0.75	Green	525.00	80.00	#21-556	€168,00 Qty 10+ €159,60	3-4 days
M37 x 0.75	Vis	550.00	300.00	#21-557	€151,00 Qty 10+ €143,45	3-4 days
M37 x 0.75	Orange	590.00	75.00	#21-558	€168,00 Qty 10+ €159,60	3-4 days
M37 x 0.75	Light Red	635.00	60.00	#21-559	€151,00 Qty 10+ €143,45	3-4 days
M37 x 0.75	Dark Red	660.00	60.00	#21-560	€151,00 Qty 10+ €143,45	3-4 days
M37 x 0.75	IR	850.00	160.00	#21-561	€151,00 Qty 10+ €143,45	In Stock
M37 x 0.75	SWIR	940.00	55.00	#28-790	€200,00	3-4 days
M37 x 0.75	SWIR	1,000.00	150.00	#28-801	€359,00	3-4 days
M37 x 0.75	SWIR	1,070.00	-	#28-856	€248,00	3-4 days
M37 x 0.75	SWIR	1,300.00	35.00	#28-823	€354,00	3-4 days
M37 x 0.75	SWIR	1,450.00	35.00	#28-834	€354,00	3-4 days
M37 x 0.75	SWIR	1,475.00	-	#28-867	€244,00	3-4 days
M37 x 0.75	SWIR	1,550.00	190.00	#28-812	€359,00	3-4 days
M37 x 0.75	SWIR	1,550.00	35.00	#28-845	€354,00	3-4 days
M35.5 x 0.50	NUV	324.00	105.00	#21-570	€158,00 Qty 10+ €150,10	3-4 days
M35.5 x 0.50	Blue	470.00	85.00	#21-571	€158,00 Qty 10+ €150,10	3-4 days

M35.5 x 0.50	Cyan	505.00	90.00	#21-572	€158,00 Qty 10+ €150,10	3-4 days
M35.5 x 0.50	Green	525.00	80.00	#21-573	€158,00 Qty 10+ €150,10	3-4 days
M35.5 x 0.50	Vis	550.00	300.00	#21-574	€142,00 Qty 10+ €134,90	In Stock
M35.5 x 0.50	Orange	590.00	75.00	#21-575	€158,00 Qty 10+ €150,10	3-4 days
M35.5 x 0.50	Light Red	635.00	60.00	#21-576	€142,00 Qty 10+ €134,90	3-4 days
M35.5 x 0.50	Dark Red	660.00	60.00	#21-577	€142,00 Qty 10+ €134,90	3-4 days
M35.5 x 0.50	IR	850.00	160.00	#21-578	€142,00 Qty 10+ €134,90	3-4 days
M35.5 x 0.50	SWIR	940.00	55.00	#28-789	€188,00	3-4 days
M35.5 x 0.50	SWIR	1,000.00	150.00	#28-800	€330,00	3-4 days
M35.5 x 0.50	SWIR	1,070.00	-	#28-855	€224,00	3-4 days
M35.5 x 0.50	SWIR	1,300.00	35.00	#28-822	€343,00	3-4 days
M35.5 x 0.50	SWIR	1,450.00	35.00	#28-833	€343,00	Contact Us
M35.5 x 0.50	SWIR	1,475.00	-	#28-866	€224,00	3-4 days
M35.5 x 0.50	SWIR	1,550.00	190.00	#28-811	€330,00	3-4 days
M35.5 x 0.50	SWIR	1,550.00	35.00	#28-844	€343,00	3-4 days
M72 x 0.75	NUV	324.00	105.00	#21-587	€376,00 Qty 10+ €357,20	3-4 days
M72 x 0.75	Blue	470.00	85.00	#21-588	€376,00 Qty 10+ €357,20	3-4 days
M72 x 0.75	Cyan	505.00	90.00	#21-589	€376,00 Qty 10+ €357,20	3-4 days

M72 x 0.75	Green	525.00	80.00	#21-590	€376,00 Qty 10+ €357,20	3-4 days
M72 x 0.75	Vis	550.00	300.00	#21-591	€339,00 Qty 10+ €322,05	Contact Us
M72 x 0.75	Orange	590.00	75.00	#21-592	€376,00 Qty 10+ €357,20	3-4 days
M72 x 0.75	Light Red	635.00	60.00	#21-593	€339,00 Qty 10+ €322,05	3-4 days
M72 x 0.75	Dark Red	660.00	60.00	#21-594	€339,00 Qty 10+ €322,05	3-4 days
M72 x 0.75	IR	850.00	160.00	#21-595	€339,00 Qty 10+ €322,05	3-4 days
M72 x 0.75	SWIR	940.00	55.00	#28-796	€448,00	3-4 days
M72 x 0.75	SWIR	1,000.00	150.00	#28-807	€650,00	3-4 days
M72 x 0.75	SWIR	1,070.00	-	#28-862	€715,00	3-4 days
M72 x 0.75	SWIR	1,300.00	35.00	#28-829	€755,00	3-4 days
M72 x 0.75	SWIR	1,450.00	35.00	#28-840	€755,00	3-4 days
M72 x 0.75	SWIR	1,475.00	-	#28-873	€705,00	3-4 days
M72 x 0.75	SWIR	1,550.00	190.00	#28-818	€650,00	3-4 days
M72 x 0.75	SWIR	1,550.00	35.00	#28-851	€755,00	3-4 days
M105 x 1.00	NUV	324.00	105.00	#21-604	€880,00 Qty 10+ €836,00	3-4 days
M105 x 1.00	Blue	470.00	85.00	#21-605	€880,00 Qty 10+ €836,00	3-4 days
M105 x 1.00	Cyan	505.00	90.00	#21-606	€880,00 Qty 10+ €836,00	3-4 days
M105 x 1.00	Green	525.00	80.00	#21-607	€880,00 Qty 10+ €836,00	3-4 days
M105 x 1.00	Vis	550.00	300.00	#21-608	€792,00 Qty 10+ €752,40	3-4 days

M105 x 1.00	Orange	590.00	75.00	#21-609	€880,00 Qty 10+ €836,00	3-4 days
M105 x 1.00	Light Red	635.00	60.00	#21-610	€792,00 Qty 10+ €752,40	3-4 days
M105 x 1.00	Dark Red	660.00	60.00	#21-611	€792,00 Qty 10+ €752,40	3-4 days
M105 x 1.00	IR	850.00	160.00	#21-612	€792,00 Qty 10+ €752,40	3-4 days
M62 x 0.75	NUV	324.00	105.00	#21-621	€293,00 Qty 10+ €278,35	3-4 days
M62 x 0.75	Blue	470.00	85.00	#21-622	€293,00 Qty 10+ €278,35	Contact Us
M62 x 0.75	Cyan	505.00	90.00	#21-623	€293,00 Qty 10+ €278,35	3-4 days
M62 x 0.75	Green	525.00	80.00	#21-624	€293,00 Qty 10+ €278,35	Contact Us
M62 x 0.75	Vis	550.00	300.00	#21-625	€263,00 Qty 10+ €249,85	Contact Us
M62 x 0.75	Orange	590.00	75.00	#21-626	€293,00 Qty 10+ €278,35	Contact Us
M62 x 0.75	Light Red	635.00	60.00	#21-627	€263,00 Qty 10+ €249,85	3-4 days
M62 x 0.75	Dark Red	660.00	60.00	#21-628	€263,00 Qty 10+ €249,85	Contact Us
M62 x 0.75	IR	850.00	160.00	#21-629	€263,00 Qty 10+ €249,85	3-4 days
M46 x 0.75	NUV	324.00	105.00	#21-638	€202,00 Qty 10+ €191,90	3-4 days
M46 x 0.75	Blue	470.00	85.00	#21-639	€202,00 Qty 10+ €191,90	Contact Us
M46 x 0.75	Cyan	505.00	90.00	#21-640	€202,00 Qty 10+ €191,90	3-4 days
M46 x 0.75	Green	525.00	80.00	#21-641	€202,00 Qty 10+ €191,90	Contact Us
M46 x 0.75	Vis	550.00	300.00	#21-642	€182,00 Qty 10+ €172,90	3-4 days
M46 x 0.75	Orange	590.00	75.00	#21-643	€202,00 Qty 10+ €191,90	Contact Us

M46 x 0.75	Light Red	635.00	60.00	#21-644	€182,00 Qty 10+ €172,90	Contact Us
M46 x 0.75	Dark Red	660.00	60.00	#21-645	€182,00 Qty 10+ €172,90	3-4 days
M46 x 0.75	IR	850.00	160.00	#21-646	€182,00 Qty 10+ €172,90	3-4 days
M46 x 0.75	SWIR	940.00	55.00	#28-793	€240,00	3-4 days
M46 x 0.75	SWIR	1,000.00	150.00	#28-804	€433,00	3-4 days
M46 x 0.75	SWIR	1,070.00	-	#28-859	€324,00	3-4 days
M46 x 0.75	SWIR	1,300.00	35.00	#28-826	€416,00	3-4 days
M46 x 0.75	SWIR	1,450.00	35.00	#28-837	€416,00	3-4 days
M46 x 0.75	SWIR	1,475.00	-	#28-870	€322,00	3-4 days
M46 x 0.75	SWIR	1,550.00	190.00	#28-815	€434,00	3-4 days
M46 x 0.75	SWIR	1,550.00	35.00	#28-848	€416,00	3-4 days
M40.5 x 0.50	NUV	324.00	105.00	#21-655	€185,00 Qty 10+ €175,75	3-4 days
M40.5 x 0.50	Blue	470.00	85.00	#21-656	€185,00 Qty 10+ €175,75	3-4 days
M40.5 x 0.50	Cyan	505.00	90.00	#21-657	€185,00 Qty 10+ €175,75	3-4 days
M40.5 x 0.50	Green	525.00	80.00	#21-658	€185,00 Qty 10+ €175,75	3-4 days
M40.5 x 0.50	Vis	550.00	300.00	#21-659	€167,00 Qty 10+ €158,65	3-4 days
M40.5 x 0.50	Orange	590.00	75.00	#21-660	€185,00 Qty 10+ €175,75	3-4 days
M40.5 x 0.50	Light Red	635.00	60.00	#21-661	€167,00 Qty 10+ €158,65	3-4 days
M40.5 x 0.50	Dark Red	660.00	60.00	#21-662	€167,00 Qty 10+ €158,65	3-4 days

M40.5 x 0.50	IR	850.00	160.00	#21-663	€167,00 Qty 10+ €158,65	3-4 days
M40.5 x 0.50	SWIR	940.00	55.00	#28-791	€220,00	3-4 days
M40.5 x 0.50	SWIR	1,000.00	150.00	#28-802	€393,00	3-4 days
M40.5 x 0.50	SWIR	1,070.00	-	#28-857	€272,00	3-4 days
M40.5 x 0.50	SWIR	1,300.00	35.00	#28-824	€406,00	3-4 days
M40.5 x 0.50	SWIR	1,450.00	35.00	#28-835	€406,00	3-4 days
M40.5 x 0.50	SWIR	1,475.00	-	#28-868	€276,00	3-4 days
M40.5 x 0.50	SWIR	1,550.00	190.00	#28-813	€393,00	3-4 days
M40.5 x 0.50	SWIR	1,550.00	35.00	#28-846	€406,00	3-4 days
M37.5 x 0.50	NUV	324.00	105.00	#21-672	€168,00 Qty 10+ €159,60	3-4 days
M37.5 x 0.50	Blue	470.00	85.00	#21-673	€168,00 Qty 10+ €159,60	3-4 days
M37.5 x 0.50	Cyan	505.00	90.00	#21-674	€168,00 Qty 10+ €159,60	3-4 days
M37.5 x 0.50	Green	525.00	80.00	#21-675	€168,00 Qty 10+ €159,60	3-4 days
M37.5 x 0.50	Vis	550.00	300.00	#21-676	€151,00 Qty 10+ €143,45	3-4 days
M37.5 x 0.50	Orange	590.00	75.00	#21-677	€168,00 Qty 10+ €159,60	3-4 days
M37.5 x 0.50	Light Red	635.00	60.00	#21-678	€151,00 Qty 10+ €143,45	Contact Us
M37.5 x 0.50	Dark Red	660.00	60.00	#21-679	€151,00 Qty 10+ €143,45	3-4 days
M37.5 x 0.50	IR	850.00	160.00	#21-680	€151,00 Qty 10+ €143,45	3-4 days

M43 x 0.75	NUV	324.00	105.00	#21-689	€185,00 Qty 10+ €175,75	3-4 days
M43 x 0.75	Blue	470.00	85.00	#21-690	€185,00 Qty 10+ €175,75	3-4 days
M43 x 0.75	Cyan	505.00	90.00	#21-691	€185,00 Qty 10+ €175,75	3-4 days
M43 x 0.75	Green	525.00	80.00	#21-692	€185,00 Qty 10+ €175,75	3-4 days
M43 x 0.75	Vis	550.00	300.00	#21-693	€167,00 Qty 10+ €158,65	3-4 days
M43 x 0.75	Orange	590.00	75.00	#21-694	€185,00 Qty 10+ €175,75	3-4 days
M43 x 0.75	Light Red	635.00	60.00	#21-695	€167,00 Qty 10+ €158,65	3-4 days
M43 x 0.75	Dark Red	660.00	60.00	#21-696	€167,00 Qty 10+ €158,65	3-4 days
M43 x 0.75	IR	850.00	160.00	#21-697	€167,00 Qty 10+ €158,65	3-4 days
M43 x 0.75	SWIR	940.00	55.00	#28-792	€220,00	3-4 days
M43 x 0.75	SWIR	1,000.00	150.00	#28-803	€393,00	3-4 days
M43 x 0.75	SWIR	1,070.00	-	#28-858	€300,00	3-4 days
M43 x 0.75	SWIR	1,300.00	35.00	#28-825	€416,00	3-4 days
M43 x 0.75	SWIR	1,450.00	35.00	#28-836	€416,00	3-4 days
M43 x 0.75	SWIR	1,475.00	-	#28-869	€296,00	3-4 days
M43 x 0.75	SWIR	1,550.00	190.00	#28-814	€393,00	3-4 days
M43 x 0.75	SWIR	1,550.00	35.00	#28-847	€416,00	3-4 days
M34 x 0.50	NUV	324.00	105.00	#21-706	€158,00 Qty 10+ €150,10	3-4 days
M34 x 0.50	Blue	470.00	85.00	#21-707	€158,00 Qty 10+ €150,10	3-4 days

M34 x 0.50	Cyan	505.00	90.00	#21-708	€158,00 Qty 10+ €150,10	3-4 days
M34 x 0.50	Green	525.00	80.00	#21-709	€158,00 Qty 10+ €150,10	3-4 days
M34 x 0.50	Vis	550.00	300.00	#21-710	€142,00 Qty 10+ €134,90	3-4 days
M34 x 0.50	Orange	590.00	75.00	#21-711	€158,00 Qty 10+ €150,10	3-4 days
M34 x 0.50	Light Red	635.00	60.00	#21-712	€142,00 Qty 10+ €134,90	3-4 days
M34 x 0.50	Dark Red	660.00	60.00	#21-713	€142,00 Qty 10+ €134,90	3-4 days
M34 x 0.50	IR	850.00	160.00	#21-714	€142,00 Qty 10+ €134,90	3-4 days
M34 x 0.50	SWIR	940.00	55.00	#28-788	€188,00	3-4 days
M34 x 0.50	SWIR	1,000.00	150.00	#28-799	€330,00	3-4 days
M34 x 0.50	SWIR	1,070.00	-	#28-854	€224,00	3-4 days
M34 x 0.50	SWIR	1,300.00	35.00	#28-821	€343,00	3-4 days
M34 x 0.50	SWIR	1,450.00	35.00	#28-832	€343,00	3-4 days
M34 x 0.50	SWIR	1,475.00	-	#28-865	€224,00	3-4 days
M34 x 0.50	SWIR	1,550.00	190.00	#28-810	€330,00	3-4 days
M34 x 0.50	SWIR	1,550.00	35.00	#28-843	€343,00	3-4 days
M58 x 0.75	NUV	324.00	105.00	#21-723	€235,00 Qty 10+ €223,25	3-4 days
M58 x 0.75	Blue	470.00	85.00	#21-724	€235,00 Qty 10+ €223,25	3-4 days
M58 x 0.75	Cyan	505.00	90.00	#21-725	€235,00 Qty 10+ €223,25	3-4 days
M58 x 0.75	Green	525.00	80.00	#21-726	€235,00 Qty 10+ €223,25	3-4 days

M58 x 0.75	Vis	550.00	300.00	#21-727	€212,00 Qty 10+ €201,40	3-4 days
M58 x 0.75	Orange	590.00	75.00	#21-728	€235,00 Qty 10+ €223,25	3-4 days
M58 x 0.75	Light Red	635.00	60.00	#21-729	€212,00 Qty 10+ €201,40	3-4 days
M58 x 0.75	Dark Red	660.00	60.00	#21-730	€212,00 Qty 10+ €201,40	3-4 days
M58 x 0.75	IR	850.00	160.00	#21-731	€212,00 Qty 10+ €201,40	3-4 days
M58 x 0.75	SWIR	940.00	55.00	#28-795	€280,00	3-4 days
M58 x 0.75	SWIR	1,000.00	150.00	#28-806	€480,00	3-4 days
M58 x 0.75	SWIR	1,070.00	-	#28-861	€364,00	3-4 days
M58 x 0.75	SWIR	1,300.00	35.00	#28-828	€499,00	3-4 days
M58 x 0.75	SWIR	1,450.00	35.00	#28-839	€499,00	3-4 days
M58 x 0.75	SWIR	1,475.00	-	#28-872	€364,00	3-4 days
M58 x 0.75	SWIR	1,550.00	190.00	#28-817	€480,00	3-4 days
M58 x 0.75	SWIR	1,550.00	35.00	#28-850	€499,00	3-4 days
M25.5 x 0.50	NUV	324.00	105.00	#21-740	€135,00 Qty 10+ €128,25	3-4 days
M25.5 x 0.50	Blue	470.00	85.00	#21-741	€135,00 Qty 10+ €128,25	3-4 days
M25.5 x 0.50	Cyan	505.00	90.00	#21-742	€135,00 Qty 10+ €128,25	3-4 days
M25.5 x 0.50	Green	525.00	80.00	#21-743	€135,00 Qty 10+ €128,25	3-4 days
M25.5 x 0.50	Vis	550.00	300.00	#21-744	€121,00 Qty 10+ €114,95	Contact Us
M25.5 x 0.50	Orange	590.00	75.00	#21-745	€135,00 Qty 10+ €128,25	3-4 days

M25.5 x 0.50	Light Red	635.00	60.00	#21-746	€121,00 Qty 10+ €114,95	3-4 days
M25.5 x 0.50	Dark Red	660.00	60.00	#21-747	€121,00 Qty 10+ €114,95	3-4 days
M25.5 x 0.50	IR	850.00	160.00	#21-748	€121,00 Qty 10+ €114,95	3-4 days
M25.5 x 0.50	SWIR	940.00	55.00	#28-786	€160,00	3-4 days
M25.5 x 0.50	SWIR	1,000.00	150.00	#28-797	€289,00	3-4 days
M25.5 x 0.50	SWIR	1,070.00	-	#28-852	€194,00	3-4 days
M25.5 x 0.50	SWIR	1,300.00	35.00	#28-819	€286,00	3-4 days
M25.5 x 0.50	SWIR	1,450.00	35.00	#28-830	€286,00	3-4 days
M25.5 x 0.50	SWIR	1,475.00	-	#28-863	€192,00	3-4 days
M25.5 x 0.50	SWIR	1,550.00	190.00	#28-808	€286,00	3-4 days
M25.5 x 0.50	SWIR	1,550.00	35.00	#28-841	€286,00	3-4 days
M30.5 x 0.50	NUV	324.00	105.00	#21-757	€145,00 Qty 10+ €137,75	3-4 days
M30.5 x 0.50	Blue	470.00	85.00	#21-758	€145,00 Qty 10+ €137,75	3-4 days
M30.5 x 0.50	Cyan	505.00	90.00	#21-759	€145,00 Qty 10+ €137,75	3-4 days
M30.5 x 0.50	Green	525.00	80.00	#21-760	€145,00 Qty 10+ €137,75	3-4 days
M30.5 x 0.50	Vis	550.00	300.00	#21-761	€130,00 Qty 10+ €123,50	3-4 days
M30.5 x 0.50	Orange	590.00	75.00	#21-762	€145,00 Qty 10+ €137,75	3-4 days
M30.5 x 0.50	Light Red	635.00	60.00	#21-763	€130,00 Qty 10+ €123,50	3-4 days
M30.5 x 0.50	Dark Red	660.00	60.00	#21-764	€130,00 Qty 10+ €123,50	3-4 days

M30.5 x 0.50	IR	850.00	160.00	#21-765	€130,00 Qty 10+ €123,50	3-4 days
M30.5 x 0.50	SWIR	940.00	55.00	#28-787	€172,00	Contact Us
M30.5 x 0.50	SWIR	1,000.00	150.00	#28-798	€307,00	3-4 days
M30.5 x 0.50	SWIR	1,070.00	-	#28-853	€208,00	3-4 days
M30.5 x 0.50	SWIR	1,300.00	35.00	#28-820	€312,00	3-4 days
M30.5 x 0.50	SWIR	1,450.00	35.00	#28-831	€312,00	3-4 days
M30.5 x 0.50	SWIR	1,475.00	-	#28-864	€208,00	3-4 days
M30.5 x 0.50	SWIR	1,550.00	190.00	#28-809	€307,00	3-4 days
M30.5 x 0.50	SWIR	1,550.00	35.00	#28-842	€312,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com