

[All Products](#) / [Lights and Illumination](#) / [Machine Vision Lighting](#) / [Spot Lights](#)

Advanced Illumination High Intensity UltraSeal Washdown Spot Lights

See More by [Advanced Illumination](#)



- IP69K Certified for Extreme Washdown Environments
- Ideal for Hygienic and Aseptic Manufacturing Applications
- Intensity of Over 60,000 Lux at 300mm Working Distance

Common Specifications

General

LED Lifetime (hours):	50,000	Number of LEDs:	25
Type of Illumination:	LED Illuminator	Manufacturer:	Advanced Illumination
Geometry:	Spot Light	Illumination Mode:	Constant

Physical & Mechanical Properties

Weight (g):	290
--------------------	-----

Hardware & Interface Connectivity

Connector:	Flying Leads		
Power Supply:	#66-855	Length of Cable (m):	2

Environmental & Durability Factors

Operating Temperature (°C):	0 to +60
------------------------------------	----------

Technical Information

Products

Color	Wavelength (nm)	Stock Number	Price	Buy
Royal Blue	455.00	#21-971	€1.365,00	3-4 days
Green	530.00	#21-972	€1.365,00	3-4 days
Red Orange	625.00	#21-973	€1.365,00	3-4 days
IR	850.00	#21-974	€1.475,00	3-4 days
IR	940.00	#21-975	€1.475,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com