

[All Products](#) / [Lasers](#) / [Laser Sources](#) / [Industrial and Pointing Lasers](#)

Pigtailed Laser Diode Modules



- Single Mode Fiber with FC/PC Connector
- 1 to 100mW Output Power and 405 to 1550nm Wavelength Options
- Integrated Driver for Easy Operation



Technical Information

Products

Wavelength (nm)	Output Power (mW)	Color	Stock Number	Price	Buy
-	-	-	#19-476	€101,00 Qty 10+ €90,50	In Stock
405.00	1	Violet	#23-752	€1.115,00 Qty 10+ €1.005,00	3-4 days
405.00	30	Violet	#23-753	€1.320,00 Qty 10+ €1.190,00	3-4 days
405.00	50	Violet	#23-754	€1.555,00 Qty 10+ €1.400,00	3-4 days
445.00	15	Blue	#23-755	€1.035,00 Qty 10+ €935,00	3-4 days
445.00	50	Blue	#23-756	€1.555,00 Qty 10+ €1.400,00	3-4 days
460.00	30	Blue	#23-757	€1.400,00 Qty 10+ €1.260,00	3-4 days
460.00	50	Blue	#23-758	€1.555,00 Qty 10+ €1.400,00	3-4 days
480.00	10	Blue	#23-759	€1.400,00 Qty 10+ €1.260,00	3-4 days
480.00	20	Blue	#23-760	€1.555,00 Qty 10+ €1.400,00	3-4 days
488.00	10	Blue-Green	#23-761	€1.195,00 Qty 10+ €1.075,00	3-4 days
488.00	30	Blue-Green	#23-762	€1.555,00 Qty 10+ €1.400,00	In Stock
495.00	10	Blue-Green	#23-763	€1.400,00 Qty 10+ €1.260,00	3-4 days
495.00	20	Blue-Green	#23-764	€1.555,00 Qty 10+ €1.400,00	3-4 days
505.00	10	Green	#23-765	€1.295,00 Qty 10+ €1.165,00	3-4 days
505.00	30	Green	#23-766	€1.555,00 Qty 10+ €1.400,00	3-4 days

520.00	5	Green	#23-767	€650,00 Qty 10+ €585,00	3-4 days
520.00	20	Green	#23-768	€1.165,00 Qty 10+ €1.050,00	3-4 days
520.00	50	Green	#23-769	€1.475,00 Qty 10+ €1.330,00	3-4 days
633.00	30	Red	#23-770	€1.295,00 Qty 10+ €1.165,00	3-4 days
633.00	50	Red	#23-771	€1.555,00 Qty 10+ €1.400,00	3-4 days
635.00	1	Red	#23-772	€570,00 Qty 10+ €515,00	3-4 days
635.00	5	Red	#23-773	€650,00 Qty 10+ €585,00	3-4 days
635.00	10	Red	#23-774	€755,00 Qty 10+ €680,00	3-4 days
635.00	50	Red	#23-775	€1.010,00 Qty 10+ €910,00	3-4 days
635.00	100	Red	#23-776	€1.555,00 Qty 10+ €1.400,00	3-4 days
658.00	5	Red	#23-777	€650,00 Qty 10+ €585,00	3-4 days
658.00	10	Red	#23-778	€725,00 Qty 10+ €655,00	3-4 days
658.00	50	Red	#23-779	€1.165,00 Qty 10+ €1.050,00	3-4 days
658.00	100	Red	#23-780	€1.505,00 Qty 10+ €1.355,00	3-4 days
670.00	5	Red	#23-781	€1.140,00 Qty 10+ €1.025,00	3-4 days
685.00	10	Red	#23-782	€1.140,00 Qty 10+ €1.025,00	3-4 days
685.00	20	Red	#23-783	€1.295,00 Qty 10+ €1.165,00	3-4 days
785.00	20	Red	#23-784	€830,00 Qty 10+ €750,00	3-4 days
785.00	50	Red	#23-785	€1.295,00 Qty 10+ €1.165,00	3-4 days

808.00	20	NIR	#23-786	€1.140,00 Qty 10+ €1.025,00	3-4 days
808.00	30	NIR	#23-787	€1.295,00 Qty 10+ €1.165,00	3-4 days
830.00	5	NIR	#23-788	€780,00 Qty 10+ €700,00	In Stock
830.00	50	NIR	#23-789	€1.295,00 Qty 10+ €1.165,00	3-4 days
830.00	100	NIR	#23-790	€1.555,00 Qty 10+ €1.400,00	3-4 days
850.00	10	NIR	#23-791	€910,00 Qty 10+ €820,00	3-4 days
850.00	50	NIR	#23-792	€1.295,00 Qty 10+ €1.165,00	3-4 days
880.00	1	NIR	#23-793	€960,00 Qty 10+ €865,00	3-4 days
905.00	50	NIR	#23-794	€1.295,00 Qty 10+ €1.165,00	3-4 days
940.00	50	NIR	#23-795	€1.295,00 Qty 10+ €1.165,00	In Stock
940.00	100	NIR	#23-796	€1.400,00 Qty 10+ €1.260,00	3-4 days
976.00	5	NIR	#23-797	€725,00 Qty 10+ €655,00	3-4 days
976.00	10	NIR	#23-798	€830,00 Qty 10+ €750,00	3-4 days
1,064.00	10	NIR	#23-799	€1.140,00 Qty 10+ €1.025,00	In Stock
1,310.00	2	NIR	#23-800	€650,00 Qty 10+ €585,00	3-4 days
1,310.00	5	NIR	#23-801	€725,00 Qty 10+ €655,00	3-4 days
1,310.00	10	NIR	#23-802	€805,00 Qty 10+ €725,00	3-4 days
1,550.00	5	NIR	#23-803	€725,00 Qty 10+ €655,00	3-4 days

1,550.00

10

NIR

[#23-804](#)

€855,00
Qty 10+ €770,00

3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com