

[All Products](#) / [Imaging Lenses](#) / [Variable Magnification Lenses](#)

Computar Motorized LensConnect Variable Focal Length Lenses



- Focus, Iris, and Zoom Controlled via Simple USB Interface
- 5 MegaPixels, 1/1.8", CS-Mount or 12 MegaPixels, 1.1", C-Mount
- 4 – 10mm, 9 – 50mm, or 16 – 96mm Variable Focal Lengths Available
- [Fixed Focal Length Options](#) Available

Common Specifications

Physical & Mechanical Properties

Iris Option:	Motorized
--------------	-----------

Hardware & Interface Connectivity

Control Interface:	USB2.0 TypeA
--------------------	--------------

Length of Cable (mm):	300 ±20
-----------------------	---------

Technical Information

Products

Title	Stock Number	Price	Buy
4 - 10mm LensConnect BH Series Variable Focal Length Lens	#29-307	€865,00	3-4 days
9 - 50mm LensConnect BH Series Variable Focal Length Lens	#29-308	€1.070,00	In Stock
16 - 96mm LensConnect BH Series Variable Focal Length Lens	#24-188	€1.940,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com