

[All Products](#) / [Imaging Lenses](#) / [Fixed Focal Length Lenses](#)

TECHSPEC® HP+ Series Fixed Focal Length Lenses



- 1.2", C-Mount Lenses
- Up to 24.5 MegaPixels, 2.74μm Pixel Size Sensors
- 16mm to 35mm Focal Length

Common Specifications

General

Imaging Lens Type:	High Performance Lens
--------------------	-----------------------

Physical & Mechanical Properties

Iris Option:	Variable
--------------	----------

Optical Properties

Maximum Image Circle (mm):	19.30	Coating:	$\lambda/4$ MgF ₂
Coating Specification:	$\lambda/4$ MgF ₂		

Sensor

Maximum Sensor Format:	1.2"
------------------------	------

Threading & Mounting

Mount:	C-Mount
--------	---------

Environmental & Durability Factors

Storage Temperature (°C):	-20 to +60 For questions regarding operating temperature please contact our support team
---------------------------	------------------------------------------------------------------------------------------

Technical Information

Products

FL (mm)	Max. Sensor Format	Aperture (f/#)	WD (mm)	Mount	Stock Number	Price	Buy
16.00	1.2"	f/2.8 – 16	100mm to ∞	C- Mount	#20-225	€950,00	3-4 days
25.00	1.2"	f/2.8 – 22	200mm to ∞	C- Mount	#20-226	€895,00	3-4 days
35.00	1.2"	f/2.8 – 16	200mm to ∞	C- Mount	#20-227	€895,00	3-4 days



Copyright 2023 | Edmund Optics, Ltd Unit 1, Opus Avenue, Nether Poppleton, York, YO26 6BL, UK

Phone: 1-800-363-1992 :

www.edmundoptics.com