

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Precision Absorptive Neutral Density (ND) Filters

Stock #16-049 3-4 DAYS



1



€100,00

ADD TO CART

Qty 1-10

€100,00

Qty 11+

€90,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
0.2 ±10% @ 550nm

Glass/Filter Number:
[SCHOTT NG11](#)

Substrate: ND Filter Glass
Coating: BBAR (450-700nm)
Index of Refraction n_d: 1.50
Surface Quality: 80-50
Transformation Temperature (°C): 481
Thickness (mm): 1.52 (nominal)
Transmission (%): 63.10
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Clear Aperture (%): 90
Transmitted Wavefront, P-V: $\lambda/4$
Parallelism (arcsec): <30
Coating Specification: R_{avg} ≤1.0% @ 450 - 700nm @ 0°

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant