

0.22NA UV/VIS Patchcord 600 Micron Fiber w/ FC Connector



Stock **#57-745** CLEARANCE [CONTACT US](#)

- 1 + **€159,95**

ADD TO CART

Qty 1+
€159,95

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Acceptance Angle (°): 25.4
Cladding Diameter (µm): 660 ±13.2
Connector: FC/PC
Minimum Bend Radius (mm): 132/66 (Continuous/Momentary)
Length (m): 1.50

Numerical Aperture NA: 0.22
Operating Temperature (°C): -40 to +100
Core Diameter (µm): 600 ±12
Type: Patchcord
Wavelength: UV/MS
Index of Refraction n_d - Core: 1.458
Index of Refraction n_d - Cladding: 1.441
Wavelength Range (nm): 190 - 1250
Numerical Aperture (NA) Tolerance: ±0.02
Jacket Material: PVC Monocoil
Jacket Diameter (mm): 4.83

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View