

0.3 OD M105 x 1.00, Machine Vision Absorptive ND Filter



Stock #21-614 3-4 DAYS

- 1 + **€363,00**

ADD TO CART

Qty 1-9
€363,00

Qty 10+
€344,40

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
0.3

Clear Aperture CA (mm):
100.00

Filter Thread:
M105 x 1.00

Substrate: ☐

ND Filter Glass
Surface Quality: 40-20
Transmission (%): 50.00
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.7
Mount Thickness Including Threads (mm): 8.5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View