

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #20-133 3-4 DAYS



1



€442,00

ADD TO CART

Qty 1-5

€442,00

Qty 6+

€397,80

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):  
12.50

Optical Density OD (Average):  
0.5 +0.10/-0.05

Substrate: ☐  
UV Grade MgF<sub>2</sub>

|                                                                 |
|-----------------------------------------------------------------|
| <b>Coating:</b><br>Metallic Based ND, with Dielectric Over-Coat |
| <b>Surface Quality:</b><br>40-20                                |
| <b>Thickness (mm):</b><br>2.00 ±0.10                            |
| <b>Transmission (%):</b><br>30.00                               |
| <b>Type:</b><br>Neutral Density Filter                          |
| <b>Blocking Wavelength Range (nm):</b><br>120 - 200             |
| <b>Clear Aperture (%):</b><br>80.00                             |
| <b>Transmitted Wavefront, P-V:</b><br>λ/4                       |
| <b>Parallelism (arcsec):</b><br>1                               |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |

---