

0.5 OD, 25mm Dia., AR Coated, IR Neutral Density Filter



Infrared (IR) Neutral Density (ND) Filters

Stock #12-244 3-4 DAYS



1



€448,00

ADD TO CART

Qty 1-10

€448,00

Qty 11+

€402,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00 ±0.2

Optical Density OD (Average):
0.5

Substrate: ☐
Germanium (Ge)

Coating: Metallic Based ND
Surface Quality: 80-50
Thickness (mm): 1.00 ±0.2
Transmission (%): 31.6
Transmission Tolerance (%): ±2.0
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 5800 - 6400
Parallelism (arcmin): <10
Clear Aperture (%): 90
Wavelength Range (µm): 5.8 - 6.4
Surface Flatness (P-V): 3 - 5λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant