

[See all 11 Products in Family](#)

## 0.50" Travel, 0.001" Grad, Micrometer Drive Mech



Drive Mechanisms

Stock #58-660 **14 In Stock**

€193<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-9	€193,00 each
Qty 10-24	€173,70 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

English **Type:**

PARKER-HANNIFIN **Manufacturer:**

### Physical & Mechanical Properties

0.5 **Travel (inches):**

0.001	<b>Graduation (inches):</b>
9.5	<b>Stem Diameter (mm):</b>
Plain/Flat	<b>Stem/Spindle:</b>
9.5	<b>Stem Length (mm):</b>
6.6 (0.26")	<b>Spindle Diameter (mm):</b>
6.35 (0.25")	<b>Min. Spindle Length (mm):</b>
13.7 (0.54")	<b>Max. Diameter (mm):</b>
60.5 (2.38")	<b>Overall Length (mm):</b>

## Hardware & Interface Connectivity

English Micrometer	<b>Type of Drive:</b>
--------------------	-----------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
<a href="#">View</a>	<b>Certificate of Conformance:</b>

## Product Details

- Micrometer, Fine Screw, Digital and Differential Options Available
  - Compatible with our [Ball Bearing Stages](#)
- These drive mechanisms add versatility to our selection of [ball bearing stages](#). Four options are available: micrometer (English and Metric), fine screw, digital, and differential. Please reference individual product descriptions to see which stages are compatible with each drive mechanism.

## Technical Information

