

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #21-615 3-4 DAYS



1



€363,00

ADD TO CART

Qty 1-9

€363,00

Qty 10+

€344,40

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
0.6

Clear Aperture CA (mm):
100.00

Filter Thread:
M105 x 1.00

Substrate:

ND Filter Glass
Surface Quality: 40-20
Transmission (%): 25.00
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.7
Mount Thickness Including Threads (mm): 8.5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View