

0.6 OD M30.5 x 0.50, Mounted Absorptive ND Filter



Stock **#59-169** ☐ In Stock

-

1

+

€38,50

ADD TO CART

Qty 1-9
€38,50
Qty 10+
€37,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average): 0.6
Clear Aperture CA (mm): 25.5
Filter Thread: M30.5 x0.50
Substrate: ☐

ND Filter Glass
Thickness with Mount (mm): 4.50
Surface Quality: 80-50
Transmission (%): 25
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 5.2 ±0.3
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 32.5 ±0.3
Mount Thickness Including Threads (mm): 7

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View