

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

0.6mW Random Polarization, Lasos Hene Laser



Stock #35-206 3-4 DAYS



1



€472,00

ADD TO CART

Qty 1+

€472,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Output Power (mW):
0.6

Polarization:
Random

Wavelength (nm):
632.80

Weight (g):
160.00

Laser Class - IEC:
3R

Power Supply:
Power Supply Required and Sold Separately.
USA: [#35-221](#)
Europe: [#35-221](#)
Japan: Not Available
Korea: Not Available
China: Not Available

Static Alignment:
Centered to Outer Cylinder: ≤0.5mm
Parallel to Outer Cylinder: ≤10

Pointing Stability (mrad/°C):
≤0.1

RMS Noise:
30Hz–10MHz ≤1%

Beam Diameter (mm):
0.49

Type of Laser:
HeNe

Beam Divergence (mrad):
≤1.70

Laser Class - CDRH:
IIIa

Length (mm):
170.00

Longitudinal Mode Spacing, Nominal (MHz):
1086.00

Diameter of Laser Head (mm):
35

Length of Laser Head (mm):
170

Regulatory Compliance

RoHS:
[Compliant](#)

Certificate of Conformance:
[View](#)