


0.9 OD 25mm Dia, Absorptive ND Filter

See More by [Hoya](#)



Stock **#46-215** 3-4 DAYS

- 1 + **€44,00**

ADD TO CART

Qty 1-10
€44,00
Qty 11+
€39,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Optical Density OD (Average):

0.9 ±0.1
Glass/Filter Number: Hoya ND-13
Substrate: ☐ ND Filter Glass
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 80-50
Transformation Temperature (°C): 535
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.5
Transmission (%): 12.5 (average)
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.1
Parallelism (mm): <0.02

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View