

0.9 OD M25.5 x 0.50, Mounted Absorptive ND Filter



Stock **#59-173** [CONTACT US](#)

-

1

+

€38,50

ADD TO CART

Qty 1-9
€38,50

Qty 10+
€37,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Optical Density OD (Average):
0.9

Clear Aperture CA (mm):
21.0

Filter Thread:
M25.5 x0.50

Substrate: ☐

ND Filter Glass
Thickness with Mount (mm): 4.50
Surface Quality: 80-50
Transmission (%): 12.5
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 400 - 700
Mount Thickness (mm): 5.2 ±0.3
Note: AR Coating: MgF ₂
Coating Specification: R _{avg} ≤1.75% @400 - 700nm
Mount Diameter (mm): 27.5 ±0.3
Mount Thickness Including Threads (mm): 7

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View