

Coherent® VHK™ Circular Beam Visible Laser Diode 0221-698-01 | 0.95mW 635nm

See More by [Coherent®](#)



Coherent® VHK™ Circular Beam Visible Laser Diode

Stock **#54-023** 3-4 DAYS

- 1 + **€550,00**

ADD TO CART

Qty 1+

€550,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
-10 to +40

Output Power (mW):
0.95

Wavelength (nm):
635.00

Power Supply:
Power Supply Required and Sold Separately.
USA: [#59-099](#)
Europe: [#35-201](#)
Japan: [#59-099](#)
Korea: [#33-771](#)
China: [#59-099](#)

Storage Temperature (°C):
-40 to +80

Power Requirement:
5-10VDC

Pointing Accuracy (mrad):
<4

Electrical Leads/ Pin Connections:
red (+), black (-), case (+)

Beam Diameter (mm):
1.1 @module face

Output Type:
Free Space

Type of Laser:
Diode

Beam Divergence (mrad):
0.70

Laser Class - CDRH:
II

Color:
Red

Current (mA):
70/200 (Typical/Maximum)

Diameter (inches):
0.580

Input Voltage (V):
5-10 DC

Length (inches):
1.32

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)