

TECHSPEC® 0° AOI, 25.0mm Square, Hot Mirror



TECHSPEC High Performance Hot Mirrors

Stock **#64-458** 3-4 DAYS

⊖ 1 ⊕ **€53,00**

ADD TO CART

Qty 1-9
€53,00
Qty 10+
€46,70
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0

Coating:
Hot Mirror, 0°

Substrate: ☐
BOROFLOAT®

Dimensions (mm): 25.0 x 25.0
Surface Quality: 80-50
Thickness (mm): 3.30
Thickness Tolerance (mm): ±0.2
Type: Shortpass Filter
Dimensional Tolerance (mm): +0.0/-0.2
Coating Specification: T _{avg} >90% @ 400 - 690nm, R _{avg} >95% @ 710 - 1150nm AR: R _{avg} <1% @ 400 - 700nm
Wavelength Range (nm): 400 - 1150
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant