

0° AOI, 50mm Dia, UV Hot Mirror



UV Hot Mirrors

Stock **#46-589** 3-4 DAYS



1



€222,00

ADD TO CART

Qty 1-9

€222,00

Qty 10+

€195,50

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle of Incidence (°):
0

Coating:
Hot Mirror, 0°

Diameter (mm):
50.00 ±0.25

Substrate: Fused Silica (Corning 7980)
Surface Quality: 80-50
Thickness (mm): 3.00
Thickness Tolerance (mm): ±0.2
Type: Shortpass Filter
Clear Aperture (%): 90
Edges: Ground
Coating Specification: R_{avg} >70% @ 800 - 1050nm T_{avg} >80% @ 245 - 460nm
Wavelength Range (nm): 245 - 1050
Surface Flatness (P-V): 3 - 5λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant