

# 1-18, 50.8 x 50.8mm NBS 1963A Resolution Target Positive



NBS 1963A Resolution Target

Stock #39-857 3-4 DAYS

⊖ 1 ⊕ **€255,00**

**ADD TO CART**

Qty 1-4  
€255,00

Qty 5+  
€243,00

Volume Pricing  
[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Coating:**  
Vacuum deposited durable chromium pattern

**Frequency (lp/mm):**  
1-18

**Substrate:**  
Float Glass

**Optical Density OD (Average):**  
≥3.0

**Pattern Size (mm):**  
45.5 x 43.0

**Dimensions (mm):**  
50.8 x 50.8 ±0.51

**Surface Quality:**  
20-10

**Thickness (mm):**  
1.50

**Type:**  
Positive

**NIST Certification:**  
No

**Changes in Frequency Steps:**  
1.1, 1.25, 1.4, 1.6, 1.8, 2.0, 2.2, 2.5, 2.8, 3.2, 3.6, 4.0,  
4.5, 5.0, 5.6, 6.3, 7.1, 8.0, 9.0, 10.0, 11.0, 12.5, 14.0,  
16.0, 18.0

**Line Width Tolerance (µm):**  
±0.5

## Regulatory Compliance

**RoHS 2015:**  
[Compliant](#)

**Certificate of Conformance:**  
[View](#)

**Reach 240:**  
[Compliant](#)

---