

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Norland Optical Adhesive NOA68TH, 1 oz. Application Bottle, #14-791

Stock **#14-791** ☒ In Stock



1



€87,00

ADD TO CART

Qty 1-4

€87,00

Qty 5+

€83,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Size (oz):

1

Glass Bonding:

Excellent

Metal Bonding:

Good

Plastic Bonding: Excellent/Good
Viscosity (cps): 20,000 - 25,000
Durability: Flexible
Index of Refraction n_d: 1.54 @ 589nm
Norland Number: 68TH
Shelf Life: 4 months
Type: Bottle
Typical Applications: Screen printable, high viscosity optical adhesive that can be UV cured and/or heat cured.
Note: Heat curing (-H suffix) adhesives are oxygen inhibited. If used on the surface of a substrate, the adhesive will need to be cured under an inert atmosphere (like nitrogen) to fully cure.
Absorption Range (nm): 350 - 380
Bonding Type: Plastic to Plastic/Glass
Energy for Full Cure (J/cm²): 4.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant