

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Norland Optical Adhesive NOA88, 1 oz. Application Bottle, #14-841

Stock **#14-841** ☐ In Stock



1



€87,00

ADD TO CART

Qty 1-4

€87,00

Qty 5+

€83,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Size (oz):

1

Glass Bonding:

Excellent

Metal Bonding:

Excellent

Plastic Bonding: Fair
Viscosity (cps): 250
Durability: Hard & Flexible
Index of Refraction n_d: 1.56 @ 589nm
Norland Number: 88
Shelf Life: 4 months
Type: Bottle
Typical Applications: Low outgassing and low viscosity for bonding glass or metal. Excellent transmission in the UV.
Absorption Range (nm): 315 - 395
Bonding Type: Glass to Glass/Metal
Energy for Full Cure (J/cm²): 5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant