

TECHSPEC® 10" Diameter x 60" FL Enhanced Aluminum, Parabolic Mirror



Stock #32-274-533 3-4 DAYS

- 1 + **€2.372,00**

ADD TO CART

Qty 1-2
€2.372,00
Qty 3+
€2.016,00
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐ BOROFLOAT®☒ SUPREMAX®

Focal Length Tolerance (%): ±1.5

Surface Quality: 60-40

Surface Accuracy:

N/8
Diameter (inches): 10.0 +0.06/-0
Diameter (mm): 254.00 +1.5/-0
Effective Focal Length EFL (inches): 60.0
Effective Focal Length EFL (mm): 1,524.00
Radius of Curvature (mm): 3,048.00
Aperture (f/#): f/6
Coating: Enhanced Aluminum (450-650nm)
Coating Specification: R _{avg} >95% @ 450 - 650nm
Coating Type: Metal
Back Surface: Ground
Clear Aperture CA (mm): 229
Edge Thickness ET (inches): 1.75
Edge Thickness ET (mm): 44.50
Type: Parabolic Mirror
Wavelength Range (μm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: ☐ 0.2 J/cm ² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant