

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 10" Diameter x 60" FL Uncoated, Parabolic Mirror



Stock #32-274-000 3-4 DAYS

- 1 + €2.072,00

ADD TO CART

Qty 1-2

€2.072,00

Qty 3+

€1.761,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Substrate: ☐ BOROFLOAT®☒ SUPREMAX®

Focal Length Tolerance (%): ±1.5

Surface Quality: 60-40

Surface Accuracy:

|                                              |
|----------------------------------------------|
| N/8                                          |
| Diameter (inches):<br>10.0 +0.06/-0          |
| Diameter (mm):<br>254.00 +1.5/-0             |
| Effective Focal Length EFL (inches):<br>60.0 |
| Effective Focal Length EFL (mm):<br>1,524.00 |
| Radius of Curvature (mm):<br>3,048.00        |
| Aperture (f/#):<br>f/6                       |
| Coating:<br>Uncoated                         |
| Coating Type:<br>Uncoated                    |
| Back Surface:<br>Ground                      |
| Clear Aperture CA (mm):<br>229               |
| Edge Thickness ET (inches):<br>1.75          |
| Edge Thickness ET (mm):<br>44.50             |
| Type:<br>Parabolic Mirror                    |

Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| RoHS:<br><a href="#">Compliant</a>                  |
| Certificate of Conformance:<br><a href="#">View</a> |