

10 lp/mm, 1" x 3", Float Glass, Ronchi Ruling



Stock **#38-258** CLEARANCE **6 In Stock**

-

1

+

€175¹⁰

ADD TO CART

Volume Pricing	
Qty 1-4	€175,10 each
Qty 5+	€166,76 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties

3.00

Length (inches):

12.7 x25.4

Pattern Size (mm):

1.10	Thickness (mm):
1.00	Width (inches):
Optical Properties	
Vacuum Deposited Chrome	Coating:
10.00	Frequency (lp/mm):
Float Glass	Substrate:
3.00	Optical Density OD (Average):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 240:

PRODUCT DETAILS

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
 - Ideal for Reticle and Field Calibration Requirements
 - Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).
- Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.