

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Advanced Illumination Medium Intensity Linear Backlights

Stock #18-639 3-4 DAYS



1



€939,00

ADD TO CART

Qty 1+

€939,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
White

Input Voltage (V):
24V

Model Number:
BL31310-WHIC

Operating Temperature (°C):
0 - 50

Dimensions (mm): 267.2 x 32.2 x 21.7
Weight (g): 286
LED Lifetime (hours): 50000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Active Area (mm): 255.2 x 25
Type of Illumination: LED Illuminator
Note: Optional Manual Intensity Adjustment #86-887 and #89-555 are Available
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant
Environmental Rating: IP50
Minimum Input Current: 0.8A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 233: Contains SVHC(s)