


[See all 4 Products in Family](#)

## 100 x 100mm, 1.1mm Thick, Uncoated, Dragontrail™ Chemically Strengthened Window



Stock #17-259 **6 In Stock**

€46<sup>00</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-5	€46,00 each
Qty 6-25	€37,00 each
Qty 26-99	€35,00 each
Need More?	<a href="#">Request Quote</a>

! Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

Protective Window **Type:**

20 **Chemical Strengthening Cycle (hours):**

Glass **Type of Window:**

## Physical & Mechanical Properties

90 x 90 **Clear Aperture CA (mm):**

100.00 x 100.00 **Dimensions (mm):**

1.10 Nominal **Thickness (mm):**

100.00 **Length (mm):**

100.00 **Width (mm):**

Protective as needed **Bevel:**

90 **Clear Aperture (%):**

Fine Ground **Edges:**

0.23 **Poisson's Ratio:**

74 **Young's Modulus (GPa):**

## Optical Properties

Uncoated **Coating:**

[Dragontrail™](#) **Substrate:**

1.51 **Index of Refraction (n<sub>d</sub>):**

80-50 **Surface Quality:**

350 - 2000 **Wavelength Range (nm):**

## Material Properties

2.48 **Density (g/cm<sup>3</sup>):**

9.8 **Coefficient of Thermal Expansion CTE (10<sup>-6</sup>/°C):**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**


[Compliant](#) **Reach 247:**

## Product Details

- Chemically Strengthened Thin Glass
- Highly Resistant to Surface Scratches
- Ideal for Electronic Displays
- [TECHSPEC® Gorilla® Glass Windows](#) Also Available

Dragontrail™ Chemically Strengthened Windows provide hardened substrates with superior strength, scratch resistance and surface quality. These thin, damage resistant windows feature a Vickers hardness of 673, making them 6x stronger than soda lime float substrates. Dragontrail™ Chemically Strengthened Windows are widely used as protective cover glass for high-end touch screen displays and analytical devices. Dragontrail's structural strength and excellent transmittance (90%) from 350 – 900nm enable many customizations including thinner profiles and custom coatings for OEM consumer and industrial applications.

## Technical Information



## Quote Your Size

---