

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #38-791 3-4 DAYS



1



€44,50

ADD TO CART

Qty 1-10

€44,50

Qty 11+

€41,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Coating:

Uncoated

Dimensional Tolerance (mm):

±0.76

Dimensions (mm):

100.00 x 100.00

Edges:

Seamed Edges
Grit: ☐ 600
Substrate: ☐ Float Glass
Thickness (mm): 1.60
Type: Ground Glass Diffuser
Wavelength Range (nm): 350 - 2000
Width (mm): 100.00
Note: Sandblasted on first surface
Length (mm): 100.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant