

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #27-501 In Stock



1



€97,00

ADD TO CART

Qty 1-10

€97,00

Qty 11+

€86,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):  
100.00 +0.0/-0.5

Effective Focal Length EFL (mm):  
200.00 @ 587.6nm

Back Focal Length BFL (mm):  
189.00

Coating:

|                                             |
|---------------------------------------------|
| Uncoated                                    |
| <b>Substrate:</b> <a href="#">N-BK7</a>     |
| <b>Surface Quality:</b><br>120-80           |
| <b>Center Thickness CT (mm):</b><br>17.00   |
| <b>Edge Thickness ET (mm):</b><br>4.12      |
| <b>Radius R<sub>1</sub> (mm):</b><br>103.50 |
| <b>Clear Aperture CA (mm):</b><br>97        |
| <b>f/#:</b><br>2.00                         |
| <b>Numerical Aperture NA:</b><br>0.25       |
| <b>Type:</b><br>Condenser Lens              |
| <b>Bevel:</b><br>Protective bevel as needed |
| <b>Wavelength Range (nm):</b><br>350 - 2200 |

### Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Reach 219:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |