

TECHSPEC® 100mm Dia. Linear Plastic Polarizer (XP42-200)



Stock #86-202 3-4 DAYS

⊖ 1 ⊕ **€90,00**

ADD TO CART

Qty 1-5

€90,00

Qty 6+

€73,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
100.00 +0.0/-0.5

Extinction Ratio:
9000:1

Substrate:
[XP42-200 on PMMA](#)

Operating Temperature (°C):
-40 to +80

Thickness (mm):
2.22 ±0.25

Transmission (%):
Single: 42
Parallel: 36
Crossed: <0.004

Type:
Linear Polarizer

Construction:
Polarizing Film on PMMA

Wavelength Range (nm):
400 - 700

Polarization Efficiency (%):
>99.98

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)
