

TECHSPEC[®] 100mm Length, T-Mount Extension Tube



Stock #52-296 20+ In Stock

-

1

+

€34^{.92} €58,20

ADD TO CART

Volume Pricing	
Qty 1-4	€58,20 €34,92 each
Qty 5-9	€51,91 €31,15 each
Qty 10-25	€48,20 €28,92 each
Need More?	Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Extension TubeType:

Extension Tube (Fixed)	Function:
Physical & Mechanical Properties	
100.0	Extension Length (mm):
103.45	Total Length (mm):
48.0	Outer Diameter (mm):
37.0	Clear Aperture CA (mm):
Threading & Mounting	
T-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

PRODUCT DETAILS

- Used for Adding a Fixed Tube Extension to Optical Systems
 - Feature Male/Female Threads at Opposite Ends
 - Black Anodized Aluminum Construction
- TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.