

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

100mW, 450nm Fiber-Coupled Laser Module



Stock #19-480 [CONTACT US](#)

1 **€800,00**

ADD TO CART

Qty 1-9

€800,00

Qty 10+

€715,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
+15 to +30

Operating Voltage (V):
5.0

Output Power (mW):

100
Spatial Mode: Fiber-Coupled
Wavelength (nm): 450.00 ±5
Length of Fiber (m): 1
Type of Laser: Diode
Laser Class - CDRH: Class IIIb
Color: Blue
Connector: SMA
Length (mm): 151.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant