

[See all 4 Products in Family](#)

>100mW, PM Fiber, YDFA



Stock **#75-540** NEW **1 In Stock**

- 1 + €6.750⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	€6.750,00 each
Need More?	Request Quote

i Prices shown are exclusive of VAT/local taxes

Product Downloads

General

Note:

USB Type-A to Type-B Cable

Physical & Mechanical Properties

Dimensions (inches):

11 x3 x8

Weight (lbs):

2 lbs

Optical Properties

1025 - 1075	Wavelength Range (nm):
Electrical	
> 28 dB	Gain (dB):
< 8 dB (1064 nm)	Noise Level:
Hardware & Interface Connectivity	
USB Type-B Connector	Connector:
IEC Connector	Power Supply:
USB 2.0 Compatible	Computer Interface:
Optical Encoder with Knob	Interface:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- Erbium (EDFA) or Ytterbium (YDFA) Doped Fiber Amplifier Options
- 1530 - 1565nm or 1025 - 1075nm Wavelength Options
- Manual and Digital (USB) Control

EDFA and YDFA Fiber Amplifiers are turnkey, bench-top Erbium (Er) or Ytterbium (Yb) doped fiber amplifiers operating within wavelength ranges of 1530 - 1565nm or 1025 - 1075nm, respectively. These amplifiers offer high-gain, low-noise amplification optimized for C-band and L-band optical communication systems with an up to >100mW output power. Able to be controlled directly from the front panel or via USB connection allowing for increased flexibility, these amplifiers are available in single mode (SM) or polarization maintaining (PM) configurations. EDFA and YDFA Fiber Amplifiers offer highly functional and intuitive control features enabling users to deploy the amplifier in various environments including research and development and automated manufacturing floors. These amplifiers are ideal for dense wavelength division multiplexing (DWDM), optical sensing, and fiber telecommunications.