

100x100mm Half Mirror Coaxial Light White



Stock #21-838 3-4 DAYS

- 1 + **€3.975,00**

ADD TO CART

Qty 1+
€3.975,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color: White
Input Voltage (V): 24
Model Number: LFV3-G-100SW
Dimensions (mm): W 110 mm x D 183 mm x H 105 mm
Weight (g): 990

Power Consumption (W):
34

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#66-855](#)
Korea: [#33-733](#)
China: [#66-855](#)

Active Area (mm):
100 mm x 102 mm

Color Temperature (K):
7000

Type of Illumination:
LED Illuminator

Manufacturer:
CCS

Geometry:
Coaxial Light

Illumination Mode:
Constant

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Reach 224:
[Contains SVHC\(s\)](#)

Certificate of Conformance:
[View](#)