

1064nm 0 - 450mW, Fiber-Coupled Laser



Fiber-Coupled Laser System

Stock **#62-698** CLEARANCE CONTACT US

- 1 + **€3.497,95**

ADD TO CART

Qty 1+

€3.497,95

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Operating Temperature (°C):
+10 to +30

Output Power (mW):
450 (Maximum)

Dimensions (mm):
76.2 L x 152.4 W x 254.0 H

Fiber Diameter (µm):
100

Wavelength (nm):

1,064.00
Weight (kg): 2.95
Wavelength Tolerance (nm): ±10
Operating Humidity: 5 to 95%, non-condensing
Modulation Frequency (kHz): DC-20, TTL
Length of Cable (m): 0.5
Beam Divergence (NA): 0.22, Nominal
Output Type: Fiber-Coupled
Type of Laser: Diode
Laser Class - CDRH: IIIb
Color: Infrared
Connector: SMA
Input Voltage (V): 100 - 240 AC
Bandwidth (nm): <3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View