

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT



HOLO/OR Diffractive Beamsplitters

Stock #14-695 3-4 DAYS



1



€1.605,00

ADD TO CART

Qty 1+

€1.605,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
18.0

Coating:
Laser V-Coat (1064nm)

Design Wavelength DWL (nm):
1064

Diameter (mm):
20.00 +0.05/-0.15

Substrate:

Fused Silica (Coming 7980)
Thickness (mm): 3.00 ±0.1
Input Beam Mode: SMor MM
Minimum Beam Diameter (mm): 3.12
Overall Efficiency (%): 79
Full Angle (°) : 0.12
Output Number of Spots: 2
Separation Angle (°): 0.12
Uniformity (%): <1
Zero Order, Relative to the Incident Beam (%): <1
Damage Threshold, Reference: ☐ See Link for More Details

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant