

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #21-391 3-4 DAYS



1



€1.500,00

ADD TO CART

Qty 1-5

€1.500,00

Qty 6+

€1.345,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00 +0.00/-0.25

Angle of Incidence (°):
0

Clear Aperture CA (mm):
21.00

Center Wavelength CWL (nm): 1,064.00
Full Width-Half Max FWHM (nm): 1.00
Substrate: ☐ Soda Lime Glass & Filter Glass
Minimum Transmission (%): >50
Type: Bandpass Filter
Note: Filter Design: Two-Cavity
Substrate Thickness (mm): 6 +0.00/-0.25

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant