

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

10° Diffusing Angle 12.5mm Unmounted



Stock #35-863 [CONTACT US](#)



1



€90,00

ADD TO CART

Qty 1-5

€90,00

Qty 6+

€67,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (°):  
±1

Diffusing Angle (°):  
10 (FWHM)

Diameter (mm):  
12.50

Dimensional Tolerance (mm):

|                                                                                                                 |
|-----------------------------------------------------------------------------------------------------------------|
| ±0.5                                                                                                            |
| <b>Operating Temperature (°C):</b><br>-30 to +100 (Maximum of 240 Hours)                                        |
| <b>Substrate:</b> <input type="checkbox"/><br>Polycarbonate                                                     |
| <b>Thickness (mm):</b><br>0.78                                                                                  |
| <b>Transmission (%):</b><br>>85                                                                                 |
| <b>Type:</b><br>Holographic Diffuser                                                                            |
| <b>Wavelength Range (nm):</b><br>400 - 700                                                                      |
| <b>Construction:</b><br>Unmounted                                                                               |
| <b>Damage Threshold, By Design:</b> <input type="checkbox"/><br>0.22 J/cm <sup>2</sup> @ 1064nm, 10ns (typical) |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |