

22.2mm Aperture, 51mm FL UV/VIS Fiber Refocusing Assembly



Fiber Refocusing Assembly

Stock #17-574 3-4 DAYS



1



€615,00

ADD TO CART

Qty 1-10

€615,00

Qty 11+

€544,50

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
28.58

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Type:
Refocusing Assembly

Wavelength Range (nm): 190 - 1250
Aperture Size: 22.2
Focal Length FL (mm): 51.00
Housing Material: Anodized Aluminum
Length (mm): 25.40
Note: Compatible with #17-567 & #17-569 Fiber Collimators
Operating Temperature (°C): -40 to 100

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
