

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #63-717-INK [CONTACT US](#)

[Other Coating Options](#)



1



€87,50

ADD TO CART

Qty 1-5

€87,50

Qty 6+

€70,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
10.00 ±0.025

Effective Focal Length EFL (mm):

15.00
Focal Length Tolerance (%): ±1
Back Focal Length BFL (mm): 10.66
Focal Length Specification Wavelength (nm): 587.6
Clear Aperture CA (mm): 9.00
Centering (arcmin): <1
Center Thickness CT (mm): 7.50 ±0.10
Center Thickness CT 1 (mm): 5.50 ±0.05
Center Thickness CT 2 (mm): 2.00 ±0.05
Radius R ₁ (mm): 10.04
Radius R ₂ (mm): -7.00
Radius R ₃ (mm): -80.71
Edge Thickness ET (mm): 6.01
Substrate:  N-BAF10 / N-SF10
Surface Quality: 40-20
f/#: 1.5
Numerical Aperture NA: 0.33
Coating: VIS-NIR (400-1000nm)
Coating Specification: R _{abs} ≤0.25% @ 880nm R _{avg} ≤1.25% @400 - 870nm R _{avg} ≤1.25% @890 - 1000nm
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Bevel: Protective bevel as needed
Type: Achromatic Lens
Wavelength Range (nm): 400 - 1000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View