


10mm Diameter, Optical Cast Plastic IR Longpass Filter



Stock **#12-763** ☐ In Stock

-

1

+

€11,00

ADD TO CART

Qty 1-49
€11,00
Qty 50+
€9,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
10.00

Density (g/cm³):
1.320 at 20°C

Diameter (inches):
0.39

Substrate: ☐

Thermoset ADC (CR-39®)
Operating Temperature (°C): 100 Continuous, 130 One Hour Max
Coating: Uncoated
Color: Black
Index of Refraction n_d: 1.501 @ 20°C
Thickness (mm): 1.50 Nominal
Transmission (%): >90 (typical)
Type: Longpass Filter
Dimensional Tolerance (mm): ±0.3
Abbe Number (v_d): 57.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View