


In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 10mm Enhanced Aluminum Coated, N-BK7 Right Angle Mirror



Stock #45-592 ☐ In Stock



1



€80,00

ADD TO CART

Qty 1-5

€80,00

Qty 6+

€64,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/8

Substrate: ☐
[N-BK7](#)

Surface Quality:
40-20

Length of Legs (mm): 10.00
Dimensional Tolerance (mm): ±0.1
Coating Specification: R_{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Angle Tolerance (arcmin): ±2
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 12.73 x 9.00
Length of Hypotenuse (mm): 14.10
Type: Right Angle Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference:  0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View