

TECHSPEC® 10mm Enhanced Aluminum Coated, UV Fused Silica Right Angle Mirror



Stock **#22-546** 3-4 DAYS

- 1 + **€190,00**

ADD TO CART

Qty 1-5
€190,00

Qty 6+
€152,00

Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Surface Flatness (P-V):
λ/20

Substrate: [Fused Silica](#) (Corning 7980)

Surface Quality:
20-10

Length of Legs (mm): 10.00
Dimensional Tolerance (mm): +0.00/-0.10
Coating Specification: R_{avg} >95% @ 450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Clear Aperture CA (mm): 12.72 x 9.00
Length of Hypotenuse (mm): 14.10
Type: Right Angle Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Angle Tolerance (arcsec): ±15
Damage Threshold, Reference: 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant