

TECHSPEC® 10mm H x 20mm L x 75mm FL Uncoated, Illumination Grade PCX Cylinder Lens



Stock **#43-861** CLEARANCE 3-4 DAYS

- 1 + **€75,95**

ADD TO CART

Qty 1+

€75,95

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Effective Focal Length EFL (mm):
75.00

Substrate: ☐
[N-BK7](#)

f#:
7.5

Numerical Aperture NA:
0.07

Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 73.72
Center Thickness CT (mm): 2.00
Center Thickness Tolerance (mm): ±0.1
Dimensional Tolerance (mm): +0.0/-0.2
Dimensions (mm): 10.0 x 20.0
Edge Thickness ET (mm): 1.67
Focal Length Tolerance (%): ±3
Radius R₁ (mm): 38.72
Surface Quality: 60-40
Tilt Tolerance (mm): ±0.1 over H
Wedge Tolerance (arcmin): 15.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View