

**TECHSPEC® 10mm Length, C-Mount Extension Tube**



Stock #54-629 **20+ In Stock**

- 1 + €33<sup>25</sup>

**ADD TO CART**

Volume Pricing	
Qty 1-4	€33,25 each
Qty 5-9	€30,10 each
Qty 10-25	€27,90 each
Need More?	<a href="#">Request Quote</a>

ⓘ Prices shown are exclusive of VAT/local taxes

Product Downloads

**General**

Extension Tube **Type:**

Extension Tube (Fixed) **Function:**

**Physical & Mechanical Properties**

10.0 **Extension Length (mm):**

14.0	<b>Total Length (mm):</b>
22.0	<b>Clear Aperture CA (mm):</b>
30.0	<b>Outer Diameter (mm):</b>

## Threading & Mounting

C-Mount	<b>Thread Type:</b>
---------	---------------------

## Regulatory Compliance

<a href="#">Compliant</a>	<b>RoHS 2015:</b>
---------------------------	-------------------

<a href="#">View</a>	<b>Certificate of Conformance:</b>
----------------------	------------------------------------

<a href="#">Compliant</a>	<b>REACH 241:</b>
---------------------------	-------------------

## Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

## Technical Information

