

TECHSPEC® 10mm NIR, 70R/30T, Non-Polarizing Cube Beamsplitter



Stock **#13-437** ☐ In Stock

⊖ 1 ⊕ **€227,00**

ADD TO CART

Qty 1-5
€227,00

Qty 6+
€177,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Beam Deviation (arcmin):
≤2

Bevel:
Protective bevel as needed

Clear Aperture (%):
>90

Coating: NIR
Coating Specification: R_{avg} <0.5% @ 720 - 1080nm
Construction: Cube
Dimensions (mm): 10.0 x 10.0 x 10.0 ±0.1
Reflection/Transmission Ratio (R/T): 70/30
Substrate: N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Wavelength Range (nm): 720 - 1080
Ts-Tp : <6%
Absolute Transmission (%): 27 ±10
Average Transmission (%): 27 ±5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View