

TECHSPEC®

10mm NIR, Lateral Displacement Non-Polarized Beamsplitter



Lateral Displacement Beamsplitters

Stock #47-540 ☒ In Stock



1



€590,00

ADD TO CART

Qty 1-5

€590,00

Qty 6+

€472,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Angle Tolerance (arcsec):
±5

Beam Separation (mm):
10.00

Clear Aperture (%):
80.00

Coating Specification: R_{avg} <0.5% @ 720 - 1080nm
Construction: Prism
Dimensional Tolerance (mm): ±0.1
Extinction Ratio: T_p - T_s <6%
P-Polarization Transmission (%): 45.00
Parallelism (arcmin): <2
S-Polarization Reflection (%): 45.00
Substrate: N-BK7
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Non-Polarizing Beamsplitter
Type of Optics: Non-Polarizing
Wavelength Range (nm): 720 - 1080

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View