

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT



Stock #49-017 3-4 DAYS



1



€155,00

ADD TO CART

Qty 1-5

€155,00

Qty 6+

€124,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Coating:

Uncoated

Substrate: 

[Fused Silica](#) (Corning 7980)

Surface Quality:

20-10

Type: Penta Prism
Dimensional Tolerance (mm): ±0.10
Angle Tolerance (arcmin): ±1
Bevel: Protective bevel as needed
Length of Legs (mm): 10.00
Image Orientation: Right-Handed
Ray Deviation (°): 90
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): λ/10

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View