

1.0" Angle Mirror Mount with Mirror



1.0" Angle Mirror Mount with Mirror

Stock **#33-504** **6 In Stock**

-

1

+

€127^{.72}

ADD TO CART

Volume Pricing	
Qty 1+	€127,72 each
Need More?	Request Quote

 Prices shown are exclusive of VAT/local taxes

Product Downloads

SPECIFICATIONS

General

Adjustable - Tip-Tilt

Type:

Square or Rectangular

Type of Optics:

Fixed mirror included		Note:
1.0" Angle		Type of Mount:
Physical & Mechanical Properties		
0.1		Weight (lbs):
Black Anodized Aluminum, Stainless Steel		Construction:
15		Fine Tilt Angle (°):
0.015		Resolution (inches):
15		Fine Tip Angle (°):
0.015		Adjustment Screw Pitch (inches):
0.75		Centerline Height (inches):
22 x22		Pre-Mounted Mirror Size (mm):
Threading & Mounting		
3.0 - 25.4		Size of Compatible Optics (mm):
¼-20		Compatible Post:
1.0 Sq.		Mounting Plate Size (inches):
Regulatory Compliance		
Compliant		RoHS 2015:
View		Certificate of Conformance:

PRODUCT DETAILS

- 1.0" or 1.5" Square Mounting Surface
- Two Fine Adjustment Screws (64-Pitch) Allow for Tilting
- Models with Pre-Mounted ¼ Mirror Available
- Straight or Angle Configuration Options Available

Small Mirror Mounts are available with a 1.0" or 1.5" square mounting surface. These optical mirror mounts feature two stainless steel fine-resolution (64-pitch) mounting screws that provide precise tilting of the mounting surface in two directions. These optical mirror mounts are suitable for mounting to most post mounts. Small Mirror Mounts are constructed of black anodized aluminum and each type has an option for an included fixed mirror. These mounts feature mounting holes in various sizes, including ¼-20 and 10-32.

TECHNICAL INFORMATION

