

[See all 22 Products in Family](#)

## 10X Focusing Lens



10X Focusing Lens



Stock **#28-779** **1 In Stock**

- 1 + €395<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1+	€395,00 each
Need More?	<a href="#">Request Quote</a>

**i** Prices shown are exclusive of VAT/local taxes

### Product Downloads

### General

**Note:**  
Use with #15-943 instead of #18-509 for uniform in-line illumination.

### Physical & Mechanical Properties

104.23      **Length (mm):**

35.00 Maximum Diameter (mm):

## Threading & Mounting

M29 x 0.75 Mounting Threads:

## Regulatory Compliance

[View](#) Certificate of Conformance:

## Product Details


- Up to 43% Smaller than Industry Standard Systems
- Optimized Performance up to 1.1" Sensor
- Ideal for Life Science and Industrial Applications
- Winner of the [2023 Bronze VSD Innovators Award](#)

Edmund Optics® 120i Plan APO Infinity Corrected Objectives are infinite conjugate microscope objectives that offer exceptional image flatness and chromatic correction over 400-700nm. These objectives were designed for a 1.1" sensor to offer a large field of view and reliable image quality for high-throughput imaging applications. Ideal for life science and machine vision applications such as microscopy, flow cytometry, pharmaceutical inspection, and assembly line or fault inspection.

These objectives won the [2023 Bronze VSD Innovators Award](#).

## Technical Information

### Compact Tube Lens System



### Standard Tube Lens System

